



1 in. 90 Degree Liquidtight Connector, Insulated

By Raco
Catalog # 3544-8



1 in. 90 Degree Liquidtight Connector, Insulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Insulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3544-8
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169354483

Dimensions

Dimensions	3.212 in x 1.711 in x 2.895 in
Height	2.895 in
Length	3.212 in

Trade Size	1 in
Weight	0.568 lb
Width	1.711 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	2730

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Specifications - 35448](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand