



# 1-1/4 in. 90 Degree Liquidtight Connector, Insulated

By Raco  
Catalog # 3545DC



1-1/4 in. 90 Degree Liquidtight Connector, Insulated

\*Representative Image

## Features

- Diecast zinc construction
- Insulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Die Cast Zinc
UPC	050169980293

## Dimensions

Dimensions	3.902 in x 2.273 in x 3.642 in
Height	3.642 in
Length	3.902 in
Trade Size	1-1/4 in
Weight	0.714 lb
Width	2.273 in

## Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	1800

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3541DC](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-3545DC-SPEC-EN | REV 6/2024