



3 in x 2 in. Switch Box, 2-27/32 in. Deep, One 1/2 in. KO & NMSC Clamps, S Bracket, Nails

By Raco
Catalog # 355

3 in x 2 in. Switch Box, 2-27/32 in. Deep, One 1/2 in. KO & NMSC Clamps, S Bracket, Nails



Features

- 3 in. x 2 in., 2-27/32 in. deep
- Non-gangable
- L clamps provided for non-metallic sheathed cable (NMSC)
- Extra wide for ease of GFCI installation
- Gauging notches at 3/8 in., 1/2 in. and 5/8 in.
- Supplied with one 1/2 in. knockout
- Includes nails to fasten box to wood stud
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	355
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169903551
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.906 in
Cubic Capacity	15.8 cu.in
Depth	2.84375 in
Height	3.375 in
Weight	0.725 lb
Width	2.125 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2700

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-1](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-355-SPEC-EN | REV 6/2024