



# 2-1/2 in. 90 Degree Liquidtight Connector, Insulated

By Raco  
Catalog # 3550



2-1/2 in. 90 Degree Liquidtight Connector, Insulated

\*Representative Image

## Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Insulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3550
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169035504

## Dimensions

Dimensions	3.938 in x 3.938 in x 9.188 in
Height	9.188 in
Length	3.938 in
Trade Size	2-1/2 in

Weight	6.162 lb
Width	3.938 in

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	252

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 3550 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Specifications - 3550](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand