



2-1/2 in. 90 Degree Liquidtight Connector, Insulated

By Raco
Catalog # 3550DC



*Representative Image

2-1/2 in. 90 Degree Liquidtight Connector, Insulated

Features

- Diecast zinc construction
- Insulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

| | |
|--------------------------|----------------------|
| Catalog Number | 3550DC |
| Conduit Type | Liquidtight |
| EU RoHS Indicator | Contact Manufacturer |
| Environmental Conditions | Wet Location |
| Fitting Type | Connectors |
| Insulation Type | Insulated |
| Material | Die Cast Zinc |
| UPC | 050169916438 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 6.392 in x 3.775 in x 5.675 in |
| Height | 5.675 in |

| | |
|------------|----------|
| Length | 6.392 in |
| Trade Size | 2-1/2 in |
| Weight | 3.24 lb |
| Width | 3.775 in |

Certifications And Compliance

| | |
|--------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
| Certified Listed | cULus Listed |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 1 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 294 |

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 3550DC Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Die Cast LiquidTight Fittings](#)
- [Specifications - 3550DC](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: Liquidtight Connectors vs. popular competitor](#)