



# 3 in. 90 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco  
Catalog # 3552-3

3 in. 90 Degree Liquidtight Connector, Insulated with Ground Lug

## Features

- Malleable iron construction of the body and nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Catalog Number	3552-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169355237

## Dimensions

Dimensions	7 in x 4.407 in x 6.986 in
------------	----------------------------



\*Representative Image

Height	6.986 in
Length	7 in
Trade Size	3 in
Weight	6.869 lb
Width	4.407 in

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 35523 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Specifications - 3552-3](#)  
[Terms and Conditions - HCC Terms & Conditions](#)