



3 in. 90 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco
Catalog # 3552-3



*Representative Image

3 in. 90 Degree Liquidtight Connector, Insulated with Ground Lug

Features

- Malleable iron construction of the body and nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169355237

Dimensions

Dimensions	7 in x 4.407 in x 6.986 in
Height	6.986 in
Length	7 in
Trade Size	3 in
Weight	6.869 lb
Width	4.407 in

Certifications And Compliance

Certified Listed	cULus Listed
Hazardous Rating(s)	Class I, Division 2 Class II Division 1 & 2 Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-4](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3552-3](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-35523-SPEC-EN | REV 6/2024