



4 in. 90 Degree Liquidtight Connector, Insulated

By Raco
Catalog # 3556DC



4 in. 90 Degree Liquidtight Connector, Insulated

*Representative Image

Features

- Diecast zinc construction
- Insulated
- Patented split gland-ring assures a perfect seal, preventing pullouts
- cULus
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3556DC
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Die Cast Zinc
UPC	050169916469

Dimensions

Dimensions	8.847 in x 5.255 in x 7.899 in
Height	7.899 in
Length	8.847 in
Trade Size	4 in
Weight	7.238 lb
Width	5.255 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	100

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3541DC](#)
[SDS - HCC SDS](#)
[Sell Sheets - Die Cast LiquidTight Fittings](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3556DC-SPEC-EN | REV 6/2024