



## 3/4 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco  
Catalog # 3563-3



3/4 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

### Features

- Malleable iron construction of the body and steel nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

### General

Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169356333

### Dimensions

Dimensions	2.8 in x 1.407 in x 2.359 in
Height	2.359 in
Length	2.8 in
Trade Size	3/4 in
Weight	0.423 lb
Width	1.407 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7350

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 3563-3](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-35633-SPEC-EN | REV 6/2024