



1 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco
Catalog # 3564-3



1 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

Features

- Malleable iron construction of the body and steel nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169356432

Dimensions

Dimensions	3 in x 1.703 in x 2.57 in
Height	2.57 in
Length	3 in
Trade Size	1 in
Weight	0.551 lb
Width	1.703 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2880

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-4](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3564-3](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-35643-SPEC-EN | REV 6/2024