



1-1/4 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco
Catalog # 3565-3



1-1/4 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

Features

- Malleable iron construction of the body and nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3565-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169356531

Dimensions

Dimensions	3.3 in x 2.25 in x 3.5 in
Height	3.5 in

Length	3.3 in
Trade Size	1-1/4 in
Weight	0.846 lb
Width	2.25 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	1440

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC-E195975-4](#)
[Product Logo - LT COND](#)
[Sales Drawings - 35653 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 35653](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand