



1-1/2 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

By Raco
Catalog # 3566-3



*Representative Image

1-1/2 in. 45 Degree Liquidtight Connector, Insulated with Ground Lug

Features

- Malleable iron construction of the body and nut
- All metallic components are zinc electroplated for added corrosion protection
- Malleable iron castings mate with other components perfectly without strain or distortion
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 2 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Catalog Number	3566-3
Conduit Type	Liquidtight
Connector Type	Grounding
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169356630

Dimensions

Dimensions	3.6 in x 2.375 in x 4.063 in
------------	------------------------------

Height	4.063 in
Length	3.6 in
Trade Size	1-1/2 in
Weight	1.31 lb
Width	2.375 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC-E195975-4](#)
- [Product Logo - LT COND](#)
- [Sales Drawings - 35663 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 3566-3](#)
- [Terms and Conditions - HCC Terms & Conditions](#)