



1/2 in. Hubs - Form 1 Liquidtight Strain Relief Cord Connector, Cable Range .125 - .250

By Raco
Catalog # 3702-1

1/2 in. Hubs - Form 1 Liquidtight Strain Relief Cord Connector,
Cable Range .125 - .250



*Representative Image

Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 1-1/2 in. Malleable Iron bodies and nuts
- Additional sizes available

General

Accessory Type	Fitting
Catalog Number	3702-1
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169370216

Dimensions

Dimensions	1.453 in x 1.063 in x 1.063 in
Form Size	1 in
Height	1.063 in
Length	1.453 in
Trade Size	1/2 in
Weight	0.168 lb
Width	1.063 in

Conductor Related

Cable Range .125 - .250 in

Certifications And Compliance

Certified Listed	
Hazardous Rating(s)	Class I, Division 2 Class II Division 1 & 2 Class III, Division 1 & 2

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	12000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT CORD](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-37021-SPEC-EN | REV 6/2024