



## 1/2 in. Hubs - Form 2 Liquidtight Strain Relief Cord Connector, Cable Range .500 - .600

By Raco  
Catalog # 3702-6

1/2 in. Hubs - Form 2 Liquidtight Strain Relief Cord Connector,  
Cable Range .500 - .600



\*Representative Image

### Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 1-1/2 in. Malleable Iron bodies and nuts
- Additional sizes available

### General

Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169370261

### Dimensions

Dimensions	1.469 in x 1.188 in x 1.188 in
Form Size	2 in
Height	1.188 in
Length	1.469 in
Trade Size	1/2 in
Weight	0.15 lb
Width	1.188 in

### Conductor Related

Cable Range	.500 - .600 in
-------------	----------------

### Certifications And Compliance

Hazardous Rating(s)	Class I, Division 2 Class II Division 1 & 2 Class III, Division 1 & 2
---------------------	---

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	12000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - LT CORD](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-37026-SPEC-EN | REV 6/2024