

# 3/4 in. Hubs - Form 3 Liquidtight Strain Relief Cord Connector, Cable Range .600 - .650

By Raco Catalog # 3703-4

3/4 in. Hubs - Form 3 Liquidtight Strain Relief Cord Connector, Cable Range .600 - .650

#### **Features**

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 1-1/2 in. Malleable Iron bodies and nuts
- Additional sizes available

### General

Catalog Number 3703-4
Conduit Type Liquidtight
Connector Type Strain-Relief
EU ROHS Indicator Contact Manufacturer
Environmental Conditions Wet Location
Fitting Type Connectors
Material Steel/Malleable Iron

050169370346

## Dimensions

UPC



\*Representative Image

Dimensions 1.484 in  $\times$  1.406 in  $\times$  1.406 in Form Size 3 in Height 1.406 in

Length 1.484 in
Trade Size 3/4 in
Weight 0.196 lb
Width 1.406 in

#### **Conductor Related**

Cable Range .600 - .650 in

#### **Certifications And Compliance**

Buy America(n) Qualified Contact Manufacturer

Hazardous Rating(s)

• Class I, Division 2

• Class II Division 1 & 2

• Class III. Division 1 & 2

#### Logistics

Carton Quantity 25
Minimum Pack Quantity 25
Pallet Quantity 7600

#### **Product Assets**

Catalogs - RACO / TayMac / Bell Full Catalog

Catalogs - Commercial Fittings Product Logo - LT CORD

SDS - HCC SDS

Specifications - 37034

Terms and Conditions - HCC Terms & Conditions