



1 in. Hubs - Form 4 Liquidtight Strain Relief Cord Connector, Cable Range .700 - .850

By Raco
Catalog # [3704-2](#)



*Representative Image

1 in. Hubs - Form 4 Liquidtight Strain Relief Cord Connector,
Cable Range .700 - .850

Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 1-1/2 in. Malleable Iron bodies and nuts
- Additional sizes available

General

Catalog Number	3704-2
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169370421

Dimensions

Dimensions	1.797 in x 1.703 in x 1.703 in
Form Size	4 in
Height	1.703 in
Length	1.797 in
Trade Size	1 in
Weight	0.316 lb
Width	1.703 in

Conductor Related

Cable Range	.700 - .850 in
-------------	----------------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2

Logistics

Carton Quantity	25
Minimum Pack Quantity	25

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT CORD](#)
[SDS - HCC SDS](#)
[Specifications - 3704-2](#)
[Terms and Conditions - HCC Terms & Conditions](#)