



1-1/2 in. Hubs - Form 6 Liquidtight Strain Relief Cord Connector, Cable Range 1.000 - 1.250

By Raco
Catalog # 3706-1

1-1/2 in. Hubs - Form 6 Liquidtight Strain Relief Cord Connector,
Cable Range 1.000 - 1.250

Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 1-1/2 in. Malleable Iron bodies and nuts
- Additional sizes available

General

Catalog Number	3706-1
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169370612

Dimensions



*Representative Image

Dimensions	2.172 in x 2.406 in x 2.406 in
Form Size	6 in
Height	2.406 in
Length	2.172 in
Trade Size	1-1/2 in
Weight	0.826 lb
Width	2.406 in

Conductor Related

Cable Range	1.000 - 1.250 in
-------------	------------------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT CORD](#)
[SDS - HCC SDS](#)
[Specifications - 3706-1](#)
[Terms and Conditions - HCC Terms & Conditions](#)