



1/2 in. Color-Coded Straight Strain Relief Cord Connector, Steel, White

By Raco
Catalog # 3722-1

1/2 in. Color-Coded Straight Strain Relief Cord Connector, Steel, White



*Representative Image

Features

- Steel construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

Application

- For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
- RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

General

Catalog Number	3722-1
Color	White
Material	Steel
UPC	050169982976

Dimensions

Dimensions	1.44 in x 1.13 in x 1.13 in
Height	1.13 in
Length	1.44 in
Trade Size	0.5 in
Weight	0.12 lb
Width	1.13 in

Certifications And Compliance

Certified Listed	cULus Listed
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Div. 2• Class II, Div. 1 & 2• Class III, Div. 1 & 2
Nema Rating	NEMA 4

Logistics

Carton Quantity	25
Minimum Pack Quantity	25

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Sell Sheets - Color-Coded Cord Grip Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)