



## 3/4 in. Color-Coded Straight Strain Relief Cord Connector, Steel, Brown

By Raco  
Catalog # 3723-4

3/4 in. Color-Coded Straight Strain Relief Cord Connector,  
Steel, Brown



\*Representative Image

### Features

- Steel construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

### Application

- For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
- RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

### General

Color	Brown
Material	Steel
UPC	050169983058

### Dimensions

Dimensions	1.5 in x 1.25 in x 1.25 in
Height	1.25 in
Length	1.5 in
Trade Size	0.75 in
Weight	0.17 lb
Width	1.25 in

### Certifications And Compliance

Certified Listed	cULus Listed
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Div. 2</li><li>• Class II, Div. 1 &amp; 2</li><li>• Class III, Div. 1 &amp; 2</li></ul>

Nema Rating	NEMA 4
-------------	--------

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	8400

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Color-Coded Cord Grip Connectors](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-37234-SPEC-EN | REV 6/2024