



1-1/4 in. Color-Coded Straight Strain Relief Cord Connector, Steel, White

By Raco
Catalog # 3725-3

1-1/4 in. Color-Coded Straight Strain Relief Cord Connector,
Steel, White



*Representative Image

Features

- Steel construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

General

Application	Color-Coded Straight Strain Relief Cord Connector, Steel RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
Color	White
Material	Steel
UPC	050169983195

Dimensions

Dimensions	2.06 in x 2 in x 2 in
Height	2 in
Length	2.06 in
Trade Size	1.25 in
Weight	0.445 lb
Width	2 in

Certifications And Compliance

Certified Listed	cULus Listed
Hazardous Rating(s)	Class I, Div. 2 Class II, Div. 1 & 2 Class III, Div. 1 & 2
Nema Rating	NEMA 4

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	6300

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Sell Sheets - Color-Coded Cord Grip Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-37253-SPEC-EN | REV 6/2024