



# 1-1/2 in. Color-Coded Straight Strain Relief Cord Connector, Steel, White

By Raco  
Catalog # [3726-3](#)

1-1/2 in. Color-Coded Straight Strain Relief Cord Connector, Steel, White



\*Representative Image

## Features

- Steel construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

## Application

- For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
- RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

## General

Color	White
Material	Steel
UPC	050169983232

## Dimensions

Dimensions	2.13 in x 2.25 in x 2.25 in
Height	2.25 in
Length	2.13 in
Trade Size	1.5 in
Weight	0.684 lb
Width	2.25 in

## Certifications And Compliance

Certified Listed	cULus Listed
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Div. 2</li><li>• Class II, Div. 1 &amp; 2</li><li>• Class III, Div. 1 &amp; 2</li></ul>

Nema Rating	NEMA 4
-------------	--------

## Logistics

Carton Quantity	10
Pallet Quantity	3360

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Color-Coded Cord Grip Connectors](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-37263-SPEC-EN | REV 6/2024