



# 1/2 in. Color-Coded 45° Strain Relief Cord Connector, Malleable Iron, White

By Raco  
Catalog # [3745-1](#)



\*Representative Image

1/2 in. Color-Coded 45° Strain Relief Cord Connector,  
Malleable Iron, White

## Features

- Malleable iron construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

## Application

- For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
- RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

## General

Color	White
Material	Malleable Iron
UPC	050169983430

## Dimensions

Dimensions	2.56 in x 1.25 in x 1.25 in
Height	1.25 in
Length	2.56 in
Trade Size	0.5 in
Weight	0.269 lb
Width	1.25 in

## Conductor Related

Cable Range	.25 - .35 in
-------------	--------------

## Certifications And Compliance

Certified Listed	cULus Listed
Nema Rating	NEMA 4

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	8400

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Color-Coded Cord Grip Connectors](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-37451-SPEC-EN | REV 6/2024