



# 3/4 in. Color-Coded 45° Strain Relief Cord Connector, Malleable Iron, Purple

By Raco  
Catalog # 3746-6

3/4 in. Color-Coded 45° Strain Relief Cord Connector, Malleable Iron, Purple



\*Representative Image

### Features

- Malleable iron construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

### General

Application	For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable  RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
Color	Purple
Material	Malleable Iron
UPC	050169983539

### Dimensions

Dimensions	2.88 in x 1.44 in x 1.44 in
Height	1.44 in
Length	2.88 in
Trade Size	0.75 in
Weight	0.372 lb
Width	1.44 in

### Conductor Related

Cable Range	.75 - .85 in
-------------	--------------

### Certifications And Compliance

Certified Listed	cULus Listed
Nema Rating	NEMA 4

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3360

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Customer Notices - Prop65\\_Cancer](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Color-Coded Cord Grip Connectors](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-37466-SPEC-EN | REV 6/2024