



1 in. Color-Coded 45° Strain Relief Cord Connector, Malleable Iron, Purple

By Raco
Catalog # 3747-3



1 in. Color-Coded 45° Strain Relief Cord Connector, Malleable Iron, Purple

*Representative Image

Features

- Malleable iron construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

General

Application	For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
Color	Purple
Material	Malleable Iron
UPC	050169983577

Dimensions

Dimensions	3.13 in x 1.75 in x 1.75 in
Height	1.75 in
Length	3.13 in
Trade Size	1 in
Weight	0.538 lb
Width	1.75 in

Conductor Related

Cable Range	.75 - .85 in
-------------	--------------

Certifications And Compliance

Certified Listed Nema Rating	cULus Listed NEMA 4
---------------------------------	------------------------

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3360

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Sell Sheets - Color-Coded Cord Grip Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-37473-SPEC-EN | REV 6/2024