



1/2 in. Hubs - Form 1 Liquidtight Strain Relief Cord Connector, Cable Range .250 - .375

By Raco
Catalog # [3782-2](#)

1/2 in. Hubs - Form 1 Liquidtight Strain Relief Cord Connector,
Cable Range .250 - .375



*Representative Image

Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 1-1/2 in. Malleable Iron bodies and nuts
- Additional sizes available

General

Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169378229

Dimensions

Dimensions	1.57 in x 1.069 in x 1.21 in
Form Size	1 in
Height	1.21 in
Length	1.57 in
Trade Size	1/2 in
Weight	0.14 lb
Width	1.069 in

Conductor Related

Cable Range	0.250 - 0.375 in
-------------	------------------

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
---------------------	---

Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	7200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT CORD](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-37822-SPEC-EN | REV 6/2024