



1/2 in. Hubs - Form 1 90 Degree Liquidtight Strain Relief Cord Connector, Cable Range .425 - .500

By Raco
Catalog # 3792-4



*Representative Image

1/2 in. Hubs - Form 1 90 Degree Liquidtight Strain Relief Cord Connector, Cable Range .425 - .500

Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- 1/2 in. to 3/4 in. Malleable Iron bodies
- 1/2 in. to 3/4 in. Steel nuts
- Additional sizes available

General

Catalog Number	3792-4
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Malleable Iron
UPC	050169379240

Dimensions

Dimensions	1.8 in x 1.047 in x 1.899 in
Form Size	1 in

Height	1.899 in
Length	1.8 in
Trade Size	1/2 in
Weight	0.216 lb
Width	1.047 in

Conductor Related

Cable Range	.425 - .500 in
-------------	----------------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Division 2 • Class II Division 1 & 2 • Class III, Division 1 & 2

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7600

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - LT CORD](#)
- [SDS - HCC SDS](#)
- [Specifications - 3792-4](#)
- [Terms and Conditions - HCC Terms & Conditions](#)