



3/4 in. Hubs - Form 3 90 Degree Liquidtight Strain Relief Cord Connector, Cable Range .700 - .850

By Raco
Catalog # 3793-5



*Representative Image

3/4 in. Hubs - Form 3 90 Degree Liquidtight Strain Relief Cord Connector, Cable Range .700 - .850

Features

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electroplated for corrosion protection
- 1/2 in. to 3/4 in. Malleable Iron bodies
- 1/2 in. to 3/4 in. Steel nuts
- Additional sizes available

General

Catalog Number	3793-5
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Malleable Iron
UPC	050169379356

Dimensions

Dimensions	2.375 in x 1.204 in x 2.227 in
Form Size	3 in
Height	2.227 in
Length	2.375 in
Trade Size	3/4 in
Weight	0.307 lb
Width	1.204 in

Conductor Related

Cable Range	.700 - .850 in
-------------	----------------

Certifications And Compliance

Certified Listed	cULus Listed
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	4800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT CORD](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-37935-SPEC-EN | REV 6/2024