



3/4 in. Color-Coded 90° Strain Relief Cord Connector, Malleable Iron, White

By Raco
Catalog # 3795-1



3/4 in. Color-Coded 90° Strain Relief Cord Connector, Malleable Iron, White

*Representative Image

Features

- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Malleable Iron construction provides mechanical strength and durability
- Metallic components are zinc plated for corrosion protection
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Male tapered thread NPT
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel

General

Application	For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
Color	White
Material	Malleable Iron
UPC	050169983300

Dimensions

Dimensions	3.25 in x 1.44 in x 1.44 in
Height	1.44 in
Length	3.25 in
Trade Size	0.75 in
Weight	0.483 lb
Width	1.44 in

Conductor Related

Cable Range .25 - .35 in

Certifications And Compliance

Certified Listed cULus Listed
Nema Rating NEMA 4

Logistics

Carton Quantity 10
Minimum Pack Quantity 10
Pallet Quantity 2520

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Sell Sheets - Color-Coded Cord Grip Connectors](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-37951-SPEC-EN | REV 6/2024