



# 1 in. Color-Coded 90° Strain Relief Cord Connector, Malleable Iron, Yellow

By Raco  
Catalog # [3796-2](#)



1 in. Color-Coded 90° Strain Relief Cord Connector, Malleable Iron, Yellow

\*Representative Image

## Features

- Malleable iron construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

## Application

- For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
- RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

## General

Color	Yellow
Material	Malleable Iron
UPC	050169983386

## Dimensions

Dimensions	3.75 in x 1.75 in x 1.75 in
Height	1.75 in
Length	3.75 in
Trade Size	1 in
Weight	0.657 lb
Width	1.75 in

## Conductor Related

Cable Range	.65 - .75 in
-------------	--------------

## Certifications And Compliance

Certified Listed	cULus Listed
Nema Rating	NEMA 4

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3360

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Color-Coded Cord Grip Connectors](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-37962-SPEC-EN | REV 6/2024