



2 in. Rigid/IMC Compression Connector, Insulated

By Raco
Catalog # 3808RAC



2 in. Rigid/IMC Compression Connector, Insulated

*Representative Image

Features

- All steel/malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Insulated
- Hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes 1/2 in. through 2 in.

General

Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel/Malleable Iron
UPC	050169538081

Dimensions

Dimensions	3 in x 2.75 in x 2.75 in
Height	2.75 in
Length	3 in
Trade Size	2 in
Weight	0.778 lb
Width	2.75 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1225

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969- 1](#)
[Product Logo - Conduit](#)
[Sales Drawings - 3808RAC](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-3808RAC-SPEC-EN | REV 6/2024