



3-3/4 in. x 2 in. Switch Box, Nongangable, 1 in. Deep, One 1/2 in. KO & NMSC Clamps

By Raco
Catalog # 404

3-3/4 in. x 2 in. Switch Box, Nongangable, 1 in. Deep, One 1/2 in.
KO & NMSC Clamps



Features

- 3-3/4 in. x 2 in., 1 in. deep
- Shallow switch box is made for use with furring strips and 1/4 in. paneling
- RACO® "D" bracket is pre-scored and can be broken off if needed
- Q clamps provided for Nonmetallic Sheathed Cable (NMSC)
- Supplied with one 1/2 in. knockouts
- 6.5 cu. in. capacity
- Non-gangable
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.25
Bracket Type	D, for Metal or Wood Studs
Catalog Number	404
EU RoHS Indicator	Contact Manufacturer
Ends Cable	2
Fire Resistance	Yes
Gangable	No
Knockouts	1/2 in
Material	Steel
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169004043
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	1.156 in
Cubic Capacity	6.5 cu.in
Depth	1 in
Height	6.25 in
Weight	0.378 lb
Width	1.969 in

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 404](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-404-SPEC-EN | REV 6/2024