



3-3/4 in. x 2 in. Switch Box, Nongangable, 1 in. Deep, NMSC Clamps

By Raco
Catalog # 405

3-3/4 in. x 2 in. Switch Box, Nongangable, 1 in. Deep, NMSC
Clamps



Features

- 3-3/4 in. x 2 in., 1 in. deep
- Shallow switch box is made for use with furring strips and 1/4 in. paneling
- RACO® "D" bracket is pre-scored and can be broken off if needed
- Q clamps provided for nonmetallic sheathed cable (NMSC)
- 6.5 cu. in. capacity
- Non-gangable
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.25
Bracket Type	D, for Metal or Wood Studs
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	No
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169004050
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	1.151 in
Cubic Capacity	6.5 cu.in
Depth	1 in
Height	6.25 in
Weight	0.37 lb
Width	1.953 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 405](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-405-SPEC-EN | REV 6/2024