



3 in. x 2 in. Switch Box, 1-1/2 in. Deep, NMSC Clamps, Plaster Ears

By Raco
Catalog # 410

3 in. x 2 in. Switch Box, 1-1/2 in. Deep, NMSC Clamps, Plaster Ears



Features

- 3 in. x 2 in., 1-1/2 in. deep
- Non-gangable
- L clamps provided for non-metallic sheathed cable (NMSC)
- Plaster ears allow a box to be used in "old work" applications
- 7.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169004104
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	1.874 in
Cubic Capacity	7.5 cu.in
Depth	1.5 in
Height	4.233 in
Weight	0.432 lb
Width	1.975 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3375

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-18](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978- 3](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-410-SPEC-EN | REV 6/2024