



3 in. x 2 in. Switch Box, Gangable, 2 in. Deep, Eight 1/2 in. KO's & Plaster Ears

By Raco
Catalog # 420



3 in. x 2 in. Switch Box, Gangable, 2 in. Deep, Eight 1/2 in. KO's & Plaster Ears

Features

- 3 in. x 2 in., 2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 10 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169004203
Wiring System	Conduit

Dimensions

Cubic Capacity	10.3 cu.in
Depth	2 in
Height	4.219 in
Weight	0.464 lb
Width	2 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	3920

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-18](#)
[Certifications - UL COC - E195978- 3](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-420-SPEC-EN | REV 6/2024