



## 3 in. x 2 in. Switch Box, Gangable, 2 in. Deep, One 1/2 in. KO & NMSC Clamps, Plaster Ears

By Raco  
Catalog # 445



3 in. x 2 in. Switch Box, Gangable, 2 in. Deep, One 1/2 in. KO & NMSC Clamps, Plaster Ears

### Features

- 3 in. x 2 in., 2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with one 1/2 in. knockout
- Plaster ears allow a box to be used in "old work" applications
- 10 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Catalog Number	445
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	Switch Box
	Box
UPC	050169004456
Wiring System	Nonmetallic Sheathed Cable

### Dimensions

Cubic Capacity	10.3 cu.in
Depth	2 in
Height	4.219 in
Weight	0.513 lb
Width	2 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed                      UL Listed

### Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	4000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-8](#)  
[Certifications - UL COC - E195978- 8](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-445-SPEC-EN | REV 6/2024