



1/2 in. Hubs Form 1 Liquidtight Strain Relief Cord Connector, Cable Range .250 - .375

By RACO
Catalog # 4702-4

1/2 in. Hubs Form 1 Liquidtight Strain Relief Cord Connector,
Cable Range .250 - .375

Features

- Nylon construction is lightweight and easy to use
- Neoprene grommet
- Resists most common industrial corrosives
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

Specifications

Buy American Compliant Certified Listed	Contact Manufacturer • UL Listed • CSA Certified
Environmental Conditions	Wet Location
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 514B
Hazardous Rating(s)	• Class I, Division 2 • Class II Division 1 & 2 • Class III, Division 1 & 2

Conductor

Cable Range	0.250 - 0.375 in
-------------	------------------

Configuration

Connector Type	Strain-Relief
----------------	---------------



Dimensions

Length	2.031 in
Trade Size	1/2 in
Form Size	2 in
Weight	0.077 lb.
Height	1.25 in
Width	1.25 in
Dimensions	2.031 in x 1.25 in x 1.25 in

General

Color	White
Conduit Type	Liquidtight
Fitting Type	Connectors
UPC	050169470244
Material	Nylon

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7600
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)