



## 3/4 in. Hubs Form 3 Liquidtight Strain Relief Cord Connector, Cable Range .375 - .500

By Raco  
Catalog # 4703-1



3/4 in. Hubs Form 3 Liquidtight Strain Relief Cord Connector,  
Cable Range .375 - .500

### Features

- Nylon construction is lightweight and easy to use
- Neoprene grommet
- Resists most common industrial corrosives
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

### General

Catalog Number	4703-1
Color	Blue
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169470312

### Dimensions

Dimensions	2.172 in x 1.484 in x 1.484 in
Form Size	3 in
Height	1.484 in
Length	2.172 in
Trade Size	3/4 in
Weight	0.121 lb
Width	1.484 in

### Conductor Related

Cable Range 0.375 - 0.500 in

### Certifications And Compliance

Buy American Compliant  
Certified Listed

Contact Manufacturer

- UL Listed
- CSA Certified
- Class I, Division 2
- Class II Division 1 & 2
- Class III, Division 1 & 2

Hazardous Rating(s)

Industry Standard(s)

UL 514B

### Logistics

Carton Quantity 15  
Minimum Pack Quantity 15

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Literature - Raco\\_Liquidtight\\_Diameter\\_Range\\_B59](#)  
[Product Logo - LT CORD](#)  
[SDS - HCC SDS](#)  
[Specifications - 4703-1](#)  
[Terms and Conditions - HCC Terms & Conditions](#)