



3/4 in. Hubs Form 3 Liquidtight Strain Relief Cord Connector, Cable Range .500 - .625

By Raco
Catalog # 4703-2



3/4 in. Hubs Form 3 Liquidtight Strain Relief Cord Connector,
Cable Range .500 - .625

Features

- Nylon construction is lightweight and easy to use
- Neoprene grommet
- Resists most common industrial corrosives
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

General

Color	Brown
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169470329

Dimensions

Dimensions	2.172 in x 1.484 in x 1.484 in
Form Size	3 in
Height	1.484 in
Length	2.172 in
Trade Size	3/4 in
Weight	0.112 lb
Width	1.484 in

Conductor Related

Cable Range	0.500 - 0.625 in
-------------	------------------

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	4560

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Literature - Raco_Liquidtight_Diameter_Range_B59](#)
- [Product Logo - LT CORD](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-47032-SPEC-EN | REV 6/2024