



## 3/4 in. Hubs Form 3 Liquidtight Strain Relief Cord Connector, Cable Range .625 - .750

By Raco  
Catalog # 4703-3



3/4 in. Hubs Form 3 Liquidtight Strain Relief Cord Connector,  
Cable Range .625 - .750

### Features

- Nylon construction is lightweight and easy to use
- Neoprene grommet
- Resists most common industrial corrosives
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

### General

Color	Yellow
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169470336

### Dimensions

Dimensions	2.172 in x 1.484 in x 1.484 in
Form Size	3 in
Height	1.484 in
Length	2.172 in
Trade Size	3/4 in
Weight	0.116 lb
Width	1.484 in

### Conductor Related

Cable Range .625 - .750 in

### Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	4560

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Literature - Raco\\_Liquidtight\\_Diameter\\_Range\\_B59](#)  
[Product Logo - LT CORD](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-47033-SPEC-EN | REV 6/2024