



## 3 in. x 2 in. Switch Box, Gangable, 2-1/4 in. Deep, One 1/2 in. KO & NMSC Clamps, Plaster Ears

By Raco  
Catalog # 471



3 in. x 2 in. Switch Box, Gangable, 2-1/4 in. Deep, One 1/2 in. KO & NMSC Clamps, Plaster Ears

### Features

- 3 in. x 2 in., 2-1/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Beveled corner boxes are designed to prevent the clamp screws from protruding into back wall
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with one 1/2 in. knockout
- Plaster ears allow a box to be used in "old work" applications
- 10.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none"><li>• Switch Box</li><li>• Box</li></ul>
UPC	050169004715
Wiring System	Nonmetallic Sheathed Cable

### Dimensions

Cubic Capacity	10.5 cu.in
Depth	2.25 in
Height	4.219 in
Weight	0.525 lb
Width	2 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3150

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Sales Drawings - 471](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-471-SPEC-EN | REV 6/2024