



3/8 in. Type B Liquidtight Straight Connector

By RACO
Catalog # 4721

3/8 in. Type B Liquidtight Straight Connector



*Representative Image

Features

- Nylon construction provides superior corrosion resistance
- Available in trade sizes 3/8 in. through 2 in.
- Includes neoprene O-ring and nylon locknuts

Application

For use in dry or wet locations when the conduit and fittings are not subject to physical damage; Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

Specifications

Certified Listed	• UL Listed • CSA Certified
Environmental Conditions	Wet Location
Nema Rating	NEMA 4X, 12 and 13

Configuration

Connector Type	SWIVEL-LOK
----------------	------------

Dimensions

Length	1.755 in
--------	----------

Trade Size	3/8 in
Weight	0.012 lb.
Height	1.14 in
Width	1.14 in
Dimensions	1.755 in x 1.14 in x 1.14 in

General

Conduit Type	Liquidtight
Fitting Type	Connectors
UPC	050169047217
Material	Nylon

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7600
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)