



# 1/2 in. Type B Liquidtight Straight Connector

By Raco  
Catalog # [4722](#)

1/2 in. Type B Liquidtight Straight Connector

## Features

- Nylon construction provides superior corrosion resistance
- Available in trade sizes 3/8 in. through 2 in.
- Includes neoprene O-ring and nylon locknuts

## Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

## General

Catalog Number	4722
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169947227

## Dimensions

Dimensions	2.14 in x 1.3 in x 1.3 in
Height	1.3 in
Length	2.14 in



\*Representative Image

Trade Size	1/2 in
Weight	0.06 lb
Width	1.3 in

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li><li>• TAA Compliant (All status valid till December 2024)</li></ul>
Nema Rating	NEMA 4X, 12 and 13

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7600

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Product Logo - LT COND](#)  
[SDS - HCC SDS](#)  
[Specifications - 4722](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand