



# 1/2 in. Type B Liquidtight Straight Connector

By Raco  
Catalog # 4722-8



1/2 in. Type B Liquidtight Straight Connector

\*Representative Image

## Features

- Nylon construction provides superior corrosion resistance
- Packaged in polybag
- Available in trade sizes 3/8 in. through 2 in.
- Includes neoprene O-ring and nylon locknut

## General

Catalog Number	4722-8
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169472286

## Dimensions

Dimensions	2.14 in x 1.3 in x 1.3 in
Height	1.3 in
Length	2.14 in
Trade Size	1/2 in
Weight	0.028 lb
Width	1.3 in

## Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

## Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	6080

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Product Logo - LT COND](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-47228-SPEC-EN | REV 6/2024