



1 in. Type B Liquidtight Straight Connector

By Raco
Catalog # 4724



1 in. Type B Liquidtight Straight Connector

*Representative Image

Features

- Nylon construction provides superior corrosion resistance
- Available in trade sizes 3/8 in. through 2 in.
- Includes neoprene O-ring and nylon locknuts

General

Application	For use in dry or wet locations when the conduit and fittings are not subject to physical damage Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance
Catalog Number	4724
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169947241

Dimensions

Dimensions	2.32 in x 1.8 in x 1.8 in
Height	1.8 in
Length	2.32 in
Trade Size	1 in
Weight	0.08 lb
Width	1.8 in

Certifications And Compliance

Certified Listed	UL Listed CSA Certified
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3040

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-4724-SPEC-EN | REV 6/2024