



1 in. Type B Liquidtight Straight Connector

By Raco
Catalog # 4724-8



1 in. Type B Liquidtight Straight Connector

*Representative Image

Features

- Nylon construction provides superior corrosion resistance
- Packaged in polybag
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 2 in.
- Includes neoprene O-ring and nylon locknut
- NEMA Type 4X, 12, and 13

General

Catalog Number	4724-8
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169472484

Dimensions

Dimensions	2.32 in x 1.8 in x 1.8 in
Height	1.8 in
Length	2.32 in
Trade Size	1 in
Weight	0.08 lb
Width	1.8 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3040

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-47248-SPEC-EN | REV 6/2024