



2 in. Type B Liquidtight Straight Connector

By Raco
Catalog # 4728

2 in. Type B Liquidtight Straight Connector

Features

- Nylon construction provides superior corrosion resistance
- Available in trade sizes 3/8 in. through 2 in.
- Includes neoprene O-ring and nylon locknuts

Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

General

Catalog Number	4728
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169047286

Dimensions

Dimensions	2.51 in x 3.05 in x 3.05 in
Height	3.05 in



Length	2.51 in
Trade Size	2 in
Weight	0.2 lb
Width	3.05 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	840

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Specifications - 4728](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand