



3 in. x 2 in. Switch Box, Gangable, 2-1/4 in. Deep, Three 1/2 in. KO's & NMSC Clamps, Leveling Bumps

By Raco
Catalog # 473



3 in. x 2 in. Switch Box, Gangable, 2-1/4 in. Deep, Three 1/2 in. KO's & NMSC Clamps, Leveling Bumps

Features

- 3 in. x 2 in. x 2-1/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Beveled corner boxes are designed to prevent the clamp screws from protruding into back wall
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with three 1/2 in. knockouts
- 10.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169004739
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Cubic Capacity	10.5 cu.in
Depth	2.25 in
Height	3.53 in
Weight	0.505 lb
Width	2 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	3520

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-473-SPEC-EN | REV 6/2024