



1/2 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position Connector

By Raco
Catalog # 4732



1/2 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position
Connector

*Representative Image

Features

- All gray nonmetallic construction provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

| | |
|--------------------------|--|
| Application | For use in dry or wet locations when the conduit and fittings are not subject to physical damage Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance |
| Catalog Number | 4732 |
| Conduit Type | Liquidtight |
| Connector Type | SWIVEL-LOK |
| Environmental Conditions | Wet Location |
| Fitting Type | Connectors |
| Material | Nylon |
| UPC | 050169947326 |

Dimensions

| | |
|------------|---------------------------|
| Dimensions | 3.27 in x 1.3 in x 1.3 in |
| Height | 1.3 in |
| Length | 3.27 in |
| Trade Size | 1/2 in |
| Weight | 0.1 lb |
| Width | 1.3 in |

Certifications And Compliance

| | |
|----------------------|--------------------|
| Certified Listed | UL Listed |
| | CSA Certified |
| Industry Standard(s) | UL 514B |
| Nema Rating | NEMA 4X, 12 and 13 |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |
| Pallet Quantity | 7200 |

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Product Logo - LT COND](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-4732-SPEC-EN | REV 6/2024