



1/2 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position Connector

By Raco
Catalog # 4732-8



*Representative Image

1/2 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position
Connector

Features

- All gray nonmetallic construction provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

General

Catalog Number	4732-8
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169473283

Dimensions

Dimensions	3.27 in x 1.3 in x 1.3 in
Height	1.3 in
Length	3.27 in
Trade Size	1/2 in
Weight	0.093 lb
Width	1.3 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	5760

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Specifications - 47328](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand