



3/4 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position Connector

By Raco
Catalog # 4733-8



*Representative Image

3/4 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position
Connector

Features

- All gray nonmetallic construction provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

General

Catalog Number	4733-8
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169047330

Dimensions

Dimensions	3.66 in x 1.53 in x 1.53 in
Height	1.53 in
Length	3.66 in
Trade Size	3/4 in
Weight	0.127 lb
Width	1.53 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	15
Minimum Pack Quantity	15

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Specifications - 4733-8](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand